



ProSense TEMPERATURE TRANSMITTER, NON-ISOLATED, Pt100 RTD INPUT, -40-140 DEG F FIXED, 4-20 mA OUTPUT, 10-36 VDC OPERATING VOLTAGE, DIN FORM B CONNECTION HEAD MOUNT, SCREW TERMINALS

XTH2-N40140F-PT1

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
8/7/2023

SHEET 1 OF 1