








CLAMPING RANGE Ø37.0 - 53.0MM [1.46 - 2.09]
SHIELDING DIAMETER 33.0 - 49.0 [1.30 - 1.93]

ITEM	QTY	PART NUMBER	MATERIAL
7	1	Ø54x2.6 O-RING	NBR
6	1	PG 48 GLAND CAP (4.ver)	Brass (Nickel Plated)
5	1	PG48 SEAL	CR
4	1	PG 48 PLASTIC INSERT (4.VERSION)	PA6 V2
3	1	PG 48/M63 EMC PRESSURE RING	Brass (Nickel Plated)
2	1	PG 48/M63 EMC SPRING	CuBe (Tin Plated)
1	1	PG 48/M63x1.5 EMC CABLE GLAND BODY (TL14)	Brass (Nickel Plated)

PARTS LIST

Reference Number / Referans No	xxx	**bimed teknik**			
Drawing Number / Resim No	TASLAK 00				
Revision Number / Değişiklik No	00	Date / Tarih	Signature / İmza	Material / Malzeme	Undefined Tolerances acc. to/ Belirtilmeyen Toleranslar
Drawn by / Çizen	M.KOCAOĞLU	08.08.2012			
Designed by / Tasarlayan	Yılmaz ALBUKREK				
Approved by / Onaylayan	Yılmaz ALBUKREK				
Scale / Ölçek 1.5:1	Form A3	M63x1.5 EMC RAKOR EURO (PG48) TL14 M63x1.5 EMC CABLE GLANDS (EURO)(PG48) TL14			
Bimed Code-/ Bimed Kodu	BMEM-E7(M63T)TL14	Customer Code / Müşteri Kodu	xxx		

18.02.2009