



EU Information

The EZTouch Panel is manufactured in compliance with European Union (EU) Directives and carries the CE mark. The EZTouch Panel has been tested under CE Test Standard #EN55011, and is listed under UL File #E209355. The following information is provided to comply with EU documentation requirements.



Please NOTE: Products with CE marks perform their required functions safely and adhere to relevant standards as specified by EU directives provided they are used according to their intended purpose and that the instructions in this manual are adhered to. The protection provided by the equipment may be impaired if this equipment is not used in accordance with this manual. Only replacement parts supplied by Automationdirect.com or its agents should be used.

Technical Support

Consult EZTouch Programming Software Help or you may find answers to your questions in the operator interface section of our web site @ www.Automationdirect.com. If you still need assistance, please call our technical support at 1-770-844-4200 or FAX us at 1-770-886-3199.

SELV Circuits

All electrical circuits connected to the communications port receptacle are rated as Safety Extra Low Voltage (SELV).

Environmental Specifications

Operating Temperature

6" Monochrome/6" Color	0 to 45 °C
8" Color	0 to 40 °C
10" Color	0 to 50 °C
15" Color	0 to 45 °C

Storage Temperature

6" Mono	-20 to +60 °C
6" Color	-25 to +60 °C
8" Color	-20 to +60 °C
10" Color	-25 to +60 °C
15" Color	-25 to +60 °C

Operating Humidity 10–95% R.H., noncondensing

Air Composition No corrosive gases permitted

Preventative Maintenance and Cleaning

No preventative maintenance is required. The EZTouch Panel touchscreen should be cleaned as needed with warm, soapy water. See Chapter 5, *Maintenance*, for a list of compatible/incompatible chemicals and compounds.