

# BRY5362CR




Corrosion Resistant Straight Blade Receptacle.

## Product Specifications

<b>Product Type</b>	Receptacle.
<b>Blade Style</b>	Straight Blade.
<b>Device Style</b>	Standard.
<b>Amperage</b>	20A
<b>Voltage</b>	125V
<b>Poles and Wires</b>	2 Pole, 3 Wire.
<b>Receptacle Type</b>	Duplex.
<b>Color</b>	Yellow.
<b>Device Material</b>	Nylon.

<b>Finish</b>	Metal parts have .0003 nickel plating to resist corrosion.
<b>Terminals</b>	Copper-Alloy.
<b>Terminal Screw</b>	Brass combination Phillips/Slotted/Robertson, accepts up to #10 AWG.
<b>Blade/Contact Material</b>	Copper-Alloy.
<b>Mounting/Assembly Screws</b>	Silicon Bronze.
<b>Self Grounding Strap</b>	Copper-Alloy.
<b>Mounting Yoke</b>	Nickel-Plated Brass.
<b>Fed Spec</b>	Verified under #WC596.
<b>UL</b>	UL Listed File #E2258- Guide RTRT.
<b>CSA</b>	CSA Certified File #LR16215- Guide #365E1.
<b>Device Complies With:</b>	NEMA Standards WD-1, WD-6 and UL498.
<b>Overseas Approvals</b>	NOM, CE.
<b>Catalog Page</b>	<a href="#">Click here for catalog page</a>



**BRYANT®**