

11692100000 Cut Sheet



Pfannenberg Filterfan exhaust fan, top external mount, 589 CFM, 230 VAC operating voltage, G4 (coarse) filter mat, NEMA 12, indoor use only, 9.02 x 9.02in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/11692100000>

Technical Specifications

Brand	Pfannenberg
Series	Filterfan
Airflow Direction	Exhaust
Item	Fan
Mounting	Top external
With Filter	Yes
With Air Flaps	No
Filter Media	G4 (coarse) filter mat
Free Airflow	589 CFM
Airflow with Grill and Filter(s)	512 CFM
Operating Voltage	230 VAC
Frequency	50/60 Hz
Power Consumption	170W

Current Draw	1.40A
Electrical Connection	3-pole clamp for up to AWG 12/4mm2 wire
Operating Temperature	-13 to +140 °F
Average Noise Level	74 dBA
NEMA Rating	12
Application	Indoor use only
IP Rating	IP54
Enclosure Cutout	9.02 x 9.02in
Housing Material	Carbon steel
Color	RAL 7035 light gray
Mounting Depth	0in
Includes	Mounting hardware, N.O./N.O. dual thermostat, intake grille, DIN rail and (3) filters mats

Agency Approvals

UL Recognized File #	Yes / UL-US-2346183-2
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/11692100000.pdf>
See store item page for other formats.