

17065710034 Cut Sheet



Pfannenberg enclosure heater, axial fan, 650W heating capacity, touch-safe PTC resistor heating element, 230 VAC operating voltage, 50/60 Hz, adjustable thermostat, N.C. (open on rise) -20 to +40 °C, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/17065710034>

Technical Specifications

Brand	Pfannenberg
Item	Enclosure heater
IP Rating	IP20
Fan Type	Axial
Heating Capacity	650W
Heating Element	Touch-safe PTC resistor
Operating Voltage	230 VAC
Hertz	50/60 Hz
Connection	2-pole plug terminal
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) -20 to +40 °C
Switching Differential	7K
Switching Tolerance	±4K
Mounting	35mm DIN rail or panel
Requires	(4) M5 screws for panel mounting

Agency Approvals

UL Recognized File #	Yes / NITW2.E175229
CE	View CE declarations
CSA File #	Yes / 70044991
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/17065710034.pdf>
See store item page for other formats.