

17103000010 Cut Sheet



Pfannenberg mechanical thermostat, adjustable, change-over 32–140 °F (0–60 °C), 5.4 °F (3K) switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/17103000010>

Technical Specifications

Brand	Pfannenberg
Item	Mechanical thermostat
IP Rating	IP20
Setpoint Type	Adjustable
Contact 1	Change-over 32–140 °F (0–60 °C)
Switching Differential	5.4 °F (3K)
Switching Tolerance	±5.4 °F (±3K)
Maximum Switching Capacity	10A resistive / 2A inductive N.C., 5A resistive / 2A inductive N.O., 30W DC
Connection	4-pole screw terminal
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Recognized File #	Yes / 20130612-E251765
CE	View CE declarations
CSA File #	Yes / 1721048
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/17103000010.pdf>
See store item page for other formats.