

17141000010 Cut Sheet



Pfannenberg thermostat, dual adjustable, N.C. (open on rise) 32–140 °F (0–60 °C), N.O. (close on rise) 32–140 °F (0–60 °C), 12.6 °F (7K) switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/17141000010>

Technical Specifications

Brand	Pfannenberg
Item	Thermostat
IP Rating	IP20
Setpoint Type	Dual adjustable
Contact 1	N.C. (open on rise) 32–140 °F (0–60 °C)
Contact 2	N.O. (close on rise) 32–140 °F (0–60 °C)
Switching Differential	12.6 °F (7K)
Switching Tolerance	±7.2 °F (±4K)
Maximum Switching Capacity	15A resistive / 2A inductive at 120 VAC, 10A resistive / 2A inductive at 240 VAC, 30W DC
Connection	4-pole screw terminal
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Recognized File #	Yes / 20130612-E251765
CE	View CE declarations
CSA File #	Yes / 1721048
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/17141000010.pdf>
See store item page for other formats.