

18182000048 Cut Sheet



Pfannenberg Datawind intake fan, side external mount, 560 CFM, 115 VAC operating voltage, G4 (medium) filter mat, NEMA 12, indoor use only, 11.46 x 11.62in enclosure cutout, RAL 9004 black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/18182000048>

Technical Specifications

Brand	Pfannenberg
Series	Datawind
Airflow Direction	Intake
Item	Fan
Mounting	Side external
With Filter	Yes
With Air Flaps	No
Filter Media	G4 (medium) filter mat
Free Airflow	560 CFM
Airflow with Grill and Filter(s)	368 CFM
Operating Voltage	115 VAC
Frequency	50/60 Hz
Power Consumption	196W
Current Draw	1.71A

Electrical Connection	6 FT Prewired Cable IEC C-13 to NEMA 5-15P
Operating Temperature	-40 to +131 °F
Average Noise Level	66 dBA
NEMA Rating	12
Application	Indoor use only
IP Rating	IP55
Enclosure Cutout	11.46 x 11.62in
Housing Material	Thermoplastic
Color	RAL 9004 black
Mounting Depth	0in
Includes	Mounting hardware, N.O./N.O. dual thermostat and DIN rail
Additional Information	Purchase exhaust grille separately

Agency Approvals

UL Recognized File #	Yes / UL-US-L175229-21-02216002-4
CE	View CE declarations
CSA File #	Yes / 293770
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/18182000048.pdf>
See store item page for other formats.