

2999-140 Cut Sheet



Maun diagonal cutters, 5.5in (140mm) overall length, induction hardened beveled cutting edges, red comfort grip handles, compound-lever action.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2999-140>

Technical Specifications

Brand	Maun
Item	Cutters
Pliers Type	Diagonal
Overall Length	5.5in (140mm)
Insulated	No
Cutting	Induction hardened beveled cutting edges
Capacity	2.0mm piano wire or 4.0mm soft wire
Handle Type	Red comfort grip handles

Application	Wire cutting
Material	High carbon steel (HCS)
Applicable Standards	ISO 5747:1995
Tool Features	Compound-lever action
Additional Information	Designed with a compound-lever action that multiplies hand force by 22 to reduce effort when cutting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document