

4961-125 Cut Sheet



Maun parallel flat nose pliers, 4.9in (125mm) overall length, induction hardened centered cutting edges, red comfort grip handles, serrated jaws, v-notch for wire gripping and integrated side cutter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/4961-125>

Technical Specifications

Brand	Maun
Item	Pliers
Pliers Type	Parallel flat nose
Overall Length	4.9in (125mm)
Insulated	No
Cutting	Induction hardened centered cutting edges
Capacity	1.6mm piano wire or 3.0mm soft wire
Handle Type	Red comfort grip handles

Application	Gripping and wire cutting
Material	High carbon steel (HCS)
Applicable Standards	ISO 5747:1995
Tool Features	Serrated jaws, v-notch for wire gripping and integrated side cutter
Additional Information	Multiplies hand force by 23 to reduce effort when cutting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document