

7146/5-V11E01AA00000 Cut Sheet



R. STAHL 7146/5 series disconnect switch, enclosed, fusible, Class J, 3-pole, 600 VAC/125 VDC, 15A, 10 kA SCCR, wall mount, front operated, 6.69 x 13.41 x 5.16in housing, switched neutral.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7146/5-V11E01AA00000>

Technical Specifications

Brand	R. STAHL
Item	Disconnect switch
Series	7146/5
Body Type	Enclosed
Load Break Capable	Yes
Fusible	Yes
Fuse Class	Class J
Number of Poles	3
Neutral Pole	Switched neutral
Voltage Rating	600 VAC/125 VDC

Amperage Rating	15A
SCCR Rating	10 kA SCCR
Horsepower Rating	10 hp
Configuration	Front operated
Handle Type	Rotary
Mounting	Wall
Housing Size	6.69 x 13.41 x 5.16in
Housing Material	Fiberglass-reinforced plastic (FRP)
Housing Rating	NEMA 3/4/4x (IP66)
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement/FM Approval

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/7146_5-V11E01AA00000.pdf
See store item page for other formats.