

7146/5-V11E04AA00000 Cut Sheet



R. STAHL 7146/5 series disconnect switch, enclosed, fusible, Class J, 3-pole, 600 VAC, 30A, 10 kA SCCR, wall mount, front operated, 6.69 x 13.41 x 5.16in housing, switched neutral.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7146/5-V11E04AA00000>

Technical Specifications

Brand	R. STAHL
Item	Disconnect switch
Series	7146/5
Body Type	Enclosed
Load Break Capable	Yes
Fusible	Yes
Fuse Class	Class J
Number of Poles	3
Neutral Pole	Switched neutral
Voltage Rating	600 VAC

Amperage Rating	30A
SCCR Rating	10 kA SCCR
Horsepower Rating	20 hp
Configuration	Front operated
Handle Type	Rotary
Mounting	Wall
Housing Size	6.69 x 13.41 x 5.16in
Housing Material	Fiberglass-reinforced plastic (FRP)
Housing Rating	NEMA 3/4/4x (IP66)
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement/FM Approval

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/7146_5-V11E04AA00000.pdf
See store item page for other formats.