

7150/5-V11D08AA00000 Cut Sheet



R. STAHL 7150/5 series disconnect switch, enclosed, fusible, Class J, 3-pole, 600 VAC/240 VDC, 125A, 25 kA SCCR, wall mount, front operated, 18.90 x 30.98 x 9.06in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7150/5-V11D08AA00000>

Technical Specifications

Brand	R. STAHL
Item	Disconnect switch
Series	7150/5
Body Type	Enclosed
Load Break Capable	Yes
Fusible	Yes
Fuse Class	Class J
Number of Poles	3
Voltage Rating	600 VAC/240 VDC
Amperage Rating	125A

SCCR Rating	25 kA SCCR
Horsepower Rating	100 hp
Configuration	Front operated
Handle Type	Rotary
Mounting	Wall
Housing Size	18.90 x 30.98 x 9.06in
Housing Material	316L stainless steel
Housing Rating	NEMA 3/4/4x (IP66)
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement/FM Approval

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/7150_5-V11D08AA00000.pdf
See store item page for other formats.