

8150/5-V11D080000000 Cut Sheet



R. STAHL 8150/5 series disconnect switch, enclosed, 3-pole, 600 VAC/240 VDC, 125A, 25 kA SCCR, wall mount, front operated, 14.17 x 28.62 x 5.90in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8150/5-V11D080000000>

Technical Specifications

Brand	R. STAHL
Item	Disconnect switch
Series	8150/5
Body Type	Enclosed
Load Break Capable	Yes
Fusible	No
Number of Poles	3
Voltage Rating	600 VAC/240 VDC
Amperage Rating	125A

SCCR Rating	25 kA SCCR
Horsepower Rating	100 hp
Configuration	Front operated
Handle Type	Rotary
Mounting	Wall
Housing Size	14.17 x 28.62 x 5.90in
Housing Material	316L stainless steel
Housing Rating	NEMA 3/4/4x (IP66)
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/8150_5-V11D080000000.pdf
See store item page for other formats.