

8150/5-V11E040000000 Cut Sheet



R. STAHL 8150/5 series disconnect switch, enclosed, 3-pole, 600 VAC, 32A, 10 kA SCCR, wall mount, front operated, 6.93 x 9.29 x 5.90in housing, switched neutral.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8150/5-V11E040000000>

Technical Specifications

Brand	R. STAHL
Item	Disconnect switch
Series	8150/5
Body Type	Enclosed
Load Break Capable	Yes
Fusible	No
Number of Poles	3
Neutral Pole	Switched neutral
Voltage Rating	600 VAC
Amperage Rating	32A

SCCR Rating	10 kA SCCR
Horsepower Rating	20 hp
Configuration	Front operated
Handle Type	Rotary
Mounting	Wall
Housing Size	6.93 x 9.29 x 5.90in
Housing Material	316L stainless steel
Housing Rating	NEMA 3/4/4x (IP66)
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/8150_5-V11E040000000.pdf
See store item page for other formats.