

DPM3-B-AT-A4R-H Cut Sheet



ProSense digital panel meter, panel mount, 9/64 DIN, 100mm 101-segment bar graph (green) LED and 8mm 4-digit (red) LED, Input: 1-channel, current/voltage/RTD/thermocouple, Output: 4-channel, current/relay, (4) 1A Form A (SPST) relays, 100–240 VAC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM3-B-AT-A4R-H>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	9/64 DIN
Display Type	100mm 101-segment bar graph (green) LED and 8mm 4-digit (red) LED
Number of Input Channels	1
Input	Current/voltage/RTD/thermocouple
Input Current Signal Range	0–20 mA and 4–20 mA
Input Voltage Signal Range	±1 VDC, -1 to +10 VDC, ±50 mV and -199.9 to +200 mV

Input Thermocouple Signal Type	J, K, E, T, R, B, S, N, C, L, U, PL2
Input RTD Signal Types	Pt50, Pt100, JPt100, Cu50 and Cu100
Number of Output Channels	4
Analog Output Type	Sourcing
Output	Current/relay
Output Current Signal Range	4–20 mA
Relay Configuration	(4) 1A Form A (SPST) relays
Operating Voltage	100–240 VAC

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DPM3-B-AT-A4R-H.pdf>
See store item page for other formats.