

# F4-CP128-1 Cut Sheet



DirectLOGIC DL405 communication module, ASCII, 3 ports, buffered, 128k program memory, 26 MHz maximum switching frequency, (1) RS-232 and (2) RS-232/RS-422/RS-485 port(s). For use with all DL405 PLCs. Commander programming software CD-ROM for Windows included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/F4-CP128-1>

## Technical Specifications

|  |  |
|--|--|
| <b>Brand</b>                                     | DirectLOGIC  |
| <b>Item</b>                                      | Communication module   |
| <b>Series</b>                                    | DL405  |
| <b>Number of Ports</b>                           | 3  |
| <b>Buffered Ports</b>                            | Yes  |
| <b>Program Memory</b>                            | 128k   |
| <b>Maximum Switching Frequency</b>               | 26 MHz   |
| <b>Communication Port and Connection Type(s)</b> | <ul style="list-style-type: none"><li>• (1) RS-232</li><li>• (2) RS-232/RS-422/RS-485</li></ul>  |
| <b>Port Protocol(s)</b>                          | ASCII BASIC  |
| <b>Port Speed(s)</b>                             | up to 115.2k baud  |
| <b>For Use With</b>                              | All DL405 PLCs   |
| <b>Includes</b>                                  | Commander programming software CD-ROM for Windows  |
| <b>Programming Software</b>                      | DirectSOFT programming software v4.0 or later  |
| <b>Dangerous Goods</b>                           | <ul style="list-style-type: none"><li>• Battery Installed: Yes</li><li>• Packaging Instructions: 970</li><li>• UN Number: UN3091</li><li>• Hazard Type: Lithium Batteries</li><li>• Battery Type: Button</li><li>• Lithium Content: 0.01</li><li>• Replacement Battery: BR1225</li><li>• Generic Battery: BR1225</li></ul> |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E139594                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |