


GV50A-2AI2AO Cut Sheet



DURApulse GV50 series analog combo module, Input: 2-channel, current/voltage, Output: 2-channel, current/voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GV50A-2AI2AO>

Technical Specifications

Brand	DURApulse
Item	Combo module
I/O Module Type	Analog
Series	GV50
Number of Input Channels	2
Input Signal Type(s)	Current/voltage
Analog Input Type	Sinking
Number of Non-Isolated Input Commons	1
Input Resolution	12-bit
Input Current Signal Range	0–20 mA and 4–20 mA

Input Voltage Signal Range	0–10 VDC
Number of Output Channels	2
Output Signal Type	Current/voltage
Analog Output Type	Sourcing
Number of Non-Isolated Output Commons	1
Output Resolution	12-bit
Output Current Signal Range	0–20 mA and 4–20 mA
Output Voltage Signal Range	0–10 VDC
For Use With	GV50 series AC drives
Includes	Screw terminal blocks

Agency Approvals

EU REACH	View EU REACH document
----------	--

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GV50A-2AI2AO.pdf>
See store item page for other formats.