


GV50A-4DI2DO Cut Sheet



DURApulse GV50 series discrete combo module, Input: 4-point, 24 VDC, sinking/sourcing selectable, Output: 2-point, 48 VDC, sinking/sourcing selectable, 25 mA/point. For use with GV50 series AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GV50A-4DI2DO>

Technical Specifications

Brand	DURApulse
Item	Combo module
I/O Module Type	Discrete
Series	GV50
Number of Input Points	4
Nominal Input Voltage	24 VDC
Discrete Input Type	Sinking/sourcing selectable
Number of Non-Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	4
Number of Output Points	2
Nominal Output Voltage	48 VDC
Discrete Output Type	Sinking/sourcing selectable
Number of Non-Isolated Discrete Output Commons	1
Number of Points per Discrete Output Common	2
Load Current	25 mA/point
For Use With	GV50 series AC drives

Agency Approvals

EU REACH	View EU REACH document
----------	--

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GV50A-4DI2DO.pdf>
See store item page for other formats.