


GV50A-6RL Cut Sheet



DURApulse GV50 series relay output module, 6-point, 250 VAC/30 VDC, (6) Form A, 6 isolated common(s), 1 point(s) per common. Screw terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GV50A-6RL>

Technical Specifications

Brand	DURApulse
Item	Output module
I/O Module Type	Relay
Series	GV50
Number of Output Points	6
Nominal Output Voltage	250 VAC/30 VDC
Relay Configuration	(6) Form A (SPST) relays
Number of Isolated Commons	6
Jumper Selectable Isolation	No
Number of Points per Common	1
Inductive Output Current	1.2A
Resistive Output Current	3A
Fuse Type	User-supplied external fuse
Includes	Screw terminal blocks

Agency Approvals

EU REACH	View EU REACH document
----------	--

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GV50A-6RL.pdf>
See store item page for other formats.