

IPS-200-AP-1F Cut Sheet



ProSense rectangular proximity limit switch, one way pendulum with 200mm plastic rod, N.O. PNP contact(s), gravity return, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IPS-200-AP-1F>

Technical Specifications

Brand	ProSense
Item	Limit switch
Switch Type	Rectangular proximity
Actuator Type	One way pendulum with 200mm plastic rod
Contact Type	N.O. PNP
Action	Gravity return
IP Rating	IP67
Operating Temperature	-25 to +70 °C
Connection	3-pin M8 quick-disconnect

Agency Approvals

UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/IPS-200-AP-1F.pdf>
See store item page for other formats.