

KLMZ-4ST-457001AZ Cut Sheet



IDEM Z-Range universal gate box, tongue (key) interlock uniquely coded RFID, 4 station, right or left hand, solenoid, 24 VDC to unlock, (1) pair OSSD safety output(s), die-cast aluminum body.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KLMZ-4ST-457001AZ>

Technical Specifications

Brand	IDEM	Holding Force	3000N
Series	Z-Range	Safety Output Type	(1) pair OSSD
Item	Gate box	Monitoring Output Type	(2) status
Gate Box Type	Universal	Indicating Type	(4) status LEDs
Actuator Type	Tongue (key) interlock uniquely coded RFID	Housing Size	47 x 380 x 57mm
Switch Configuration	4 station	Body Material	Die-cast aluminum
Door Type	Right or left hand	Head Material	316 stainless steel
Lock Type	Solenoid, 24 VDC to unlock	IP Rating	IP65
Rear Release	No	Connection	(3) M20 cable entry
Head Type	360-degree adjustable	Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/KLMZ-4ST-457001AZ.pdf>
See store item page for other formats.