

KLMZ-4STRR-457011AZ Cut Sheet



IDEM Z-Range universal gate box, tongue (key) interlock uniquely coded RFID, 4 station, right or left hand, solenoid, 24 VDC to unlock, with rear release, (1) pair OSSD safety output(s), die-cast aluminum body.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KLMZ-4STRR-457011AZ>

Technical Specifications

Brand	IDEM
Series	Z-Range
Item	Gate box
Gate Box Type	Universal
Actuator Type	Tongue (key) interlock uniquely coded RFID
Switch Configuration	4 station
Door Type	Right or left hand
Lock Type	Solenoid, 24 VDC to unlock
Rear Release	Yes
Head Type	360-degree adjustable

Holding Force	3000N
Safety Output Type	(1) pair OSSD
Monitoring Output Type	(2) status
Indicating Type	(4) status LEDs
Housing Size	47 x 380 x 157mm
Body Material	Die-cast aluminum
Head Material	316 stainless steel
IP Rating	IP65
Connection	(3) M20 cable entry
Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/KLMZ-4STRR-457011AZ.pdf>
See store item page for other formats.