

LPM5 Cut Sheet



Mindman pneumatic threaded fitting, hex head plug, nickel-plated brass body, nickel-plated brass threads, Buna-N O-ring seal(s), M5 x 0.8 male ISO. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LPM5>

Technical Specifications

Brand	Mindman
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Threaded
Fitting Type	Hex head plug
Body Material	Nickel-plated brass
Thread Material	Nickel-plated brass

Thread Sealant	No
Seal Material	Buna-N O-ring
Fitting Measurement Type	Metric
Connection	M5 x 0.8 male ISO
Operating Pressure	145 psi
Operating Temperature	32–140 °F
Quantity per Pack	5

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement