


MCHC240 Cut Sheet



Mindman pneumatic gripper, parallel, double acting, 40mm bore, 30mm stroke, side mount grip, anodized aluminum body, M5 x 0.8 female ISO port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MCHC240>

Technical Specifications

Brand	Mindman
Item	Gripper
Working Fluid	Air or inert gas
Grip Type	Parallel
Action Type	Double acting
Bore Diameter	40mm
Stroke	30mm
Grip Mount Style	Side

Body Material	Anodized aluminum
Port Size	M5 x 0.8 female ISO
Repeatability	±0.02mm
Cycle Rate	60 cyc/min
Resulting Gripper Travel	30mm
Minimum Operating Pressure	15 psi
Maximum Operating Pressure	101 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MCHC240.pdf>
See store item page for other formats.