


MCJQ3122530M Cut Sheet



Mindman pneumatic cylinder, compact extruded, 25mm bore, 12mm rod diameter, 30mm stroke, double acting, magnetic piston, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MCJQ3122530M>

Technical Specifications

Brand	Mindman	Magnetic Piston	Yes
Item	Cylinder	Adjustable Cushions	No
Working Fluid	Air or inert gas	Body Material	Anodized aluminum
Cylinder Type	Compact extruded	End Cap Material	Anodized aluminum
Bore Diameter	25mm	Rod Material	Chrome-plated steel
Stroke	30mm	Rod Diameter	12mm
Port Size	M5 x 0.8 female ISO	Rod Thread Size	M6 x 1.0 female ISO
Mounting	Tapped end caps	Minimum Operating Pressure	8 psi
Action Type	Double acting	Maximum Operating Pressure	145 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MCJQ3122530M.pdf>
See store item page for other formats.