

MCRQ220RNPT Cut Sheet



Mindman pneumatic rotary actuator, double acting, 20mm, 0–190 degrees, shock absorbers, anodized aluminum body, 1/8in female NPT port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MCRQ220RNPT>

Technical Specifications

Brand	Mindman
Item	Rotary actuator
Working Fluid	Air or inert gas
Action Type	Double acting
Size	20mm
Adjustable Travel	0–190 degrees
Cushion Type	Shock absorbers
Body Material	Anodized aluminum
Port Size	1/8in female NPT
Minimum Operating Pressure	14.5 psi
Maximum Operating Pressure	87 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MCRQ220RNPT.pdf>
See store item page for other formats.