

MS532-18N-SS2 Cut Sheet



NITRA pneumatic push-to-connect fitting, straight, 316 stainless steel body, 316 stainless steel threads, (1) 1/8in male NPT to (1) 5/32in (4mm) push-to-connect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS532-18N-SS2>

Technical Specifications

Brand	NITRA	Thread Sealant	No
Item	Fitting	Fitting Measurement Type	Metric and SAE
Working Fluid	Air or inert gas	Connection	(1) 1/8in male NPT and (1) 5/32in (4mm) push-to-connect
Fitting Connection Type	Push-to-connect	Operating Pressure	-29.5in Hg to 290 psi
Fitting Type	Straight	Operating Temperature	32–302 °F
Body Material	316 stainless steel	For Use With	Flexible pneumatic tubing
Thread Material	316 stainless steel		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MS532-18N-SS2.pdf>
See store item page for other formats.