

RW-EKL-2-C-3.5-6.35 Cut Sheet



PBC Compact drive coupling, jaw type, aluminum, clamp, size 16, 3.5 x 6.35mm bore. For use with PBC Compact series actuators.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RW-EKL-2-C-3.5-6.35>

Technical Specifications

Brand	PBC
Item	Drive coupling
Coupling Type	Jaw type
Series	Compact
Material	Aluminum
Rated Torque	0.5 N·m
Maximum Torque	1 N·m
Slip Torque	0.5 N·m
Maximum Angular Misalignment	1.2 degrees
Maximum Parallel Misalignment	0.2mm

Maximum RPM	15000
Attachment Style	Clamp
Coupling Size	16
Overall Length	20mm
Bore Diameter	3.5mm
Bore Diameter 2	6.35mm
Outside Diameter	16mm
Clamp Screw Fastening Torque	0.6 N·m
Clamp Screw Size	M2-0.4 x 6mm
For Use With	PBC Compact series actuators

Agency Approvals

UL Listed File #	none
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RW-EKL-2-C-3.5-6.35.pdf>
See store item page for other formats.