

T17441 Cut Sheet



TITAN ExoDrive pass-through ratchet and socket set, internal spline, 6pt. internal hex, Phillips, slotted, external hex, square and Torx, 41 pieces, chrome-vanadium steel, 1/4in and 3/8in drive, imperial and metric, pass-through socket design and low profile, plastic case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T17441>

Technical Specifications

Brand	TITAN
Series	ExoDrive
Item	Ratchet and socket set
Number of Pieces	41
Socket Type (NP)	Pass-through
Impact Rated	No
Measurement Type	Imperial and metric
Material	Chrome-vanadium steel
Finish	Chrome
Insulated	No
Drive Size	1/4in and 3/8in
Tip Type	Internal spline, 6pt. internal hex, Phillips, slotted, external hex, square and Torx
Ratcheting	Yes
Directional Change	Switch lever
Return Angle	5 degrees
Lock Mechanism	Snap-in

Set Includes	Includes (11) 13mm Pass-Through spline sockets (3/16in-4.5mm, 13/64in-5mm, 7/32in-5.5mm, 1/4in-6mm, 9/32in-7mm, 5/16in-8mm, 11/32in-9mm, 3/8in-10mm, 7/16in-11mm, 15/32in-12mm, and 1/2in-13mm, (11) 19mm Pass-Through spline sockets(5/16in -8mm, 3/8in-10mm, 7/16in-11mm, 15/32in-12mm, 1/2in-13mm, 9/16in-14mm, 19/32in-15mm, 5/8in-16mm, 11/16in-17mm, 23/32in-18mm, and 3/4in-19mm), (2) quick release adapters (1/4in and 3/8in), (2) socket adapters(1/4in x 13mm and 3/8in x 19mm), (1) 1/4in bit adapter, (2) extension bars (13mm x 3in and 19mm x 3in), (2) pass-through ratchets (13mm and 19mm), (2) Phillips bits (#1 and #2), (2) slotted bits (4mm and 5.5 mm), (3) torx bits (T10, T15, and T20), (3) external hex bits (4mm, 5mm, and 6 mm)
Application	Fastening, ratcheting, screwdriving and bit holding
Package Type	Plastic case
Tool Features	Pass-through socket design and low profile

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document