

T18181 Cut Sheet



TITAN standard ratchet and socket set, 6pt. internal hex, 19 pieces, steel, 3/8in drive, imperial and metric, plastic storage rail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T18181>

Technical Specifications

Brand	TITAN	Ratcheting	Yes
Item	Ratchet and socket set	Directional Change	Dial switch
Number of Pieces	19	Return Angle	8 degrees
Socket Type (NP)	Standard	Lock Mechanism	Ballpoint socket
Impact Rated	No	Set Includes	Includes (18) standard sockets (3/8in, 7/16in, 15/32in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 9mm, 10mm, 11mm, 12mm, 13mm, 14mm, 15mm, 17mm, and 19mm), (1) quick-release ratchet
Measurement Type	Imperial and metric	Application	Ratcheting and fastening
Material	Steel	Package Type	Plastic storage rail
Finish	Chrome		
Insulated	No		
Drive Size	3/8in		
Tip Type	6pt. internal hex		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document