

T66840 Cut Sheet



TITAN AutoFlex low profile socket set, 12pt. internal hex, 7 pieces, chrome-vanadium steel, 1/4in drive, metric, flex joint springs back to center and low profile, plastic storage rail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T66840>

Technical Specifications

Brand	TITAN	Drive Size	1/4in
Series	AutoFlex	Tip Type	12pt. internal hex
Item	Socket set	Ratcheting	No
Number of Pieces	7	Set Includes	Includes (7) low profile 12pt socket set with autoflexing (6mm, 7mm, 8mm, 10mm, 11mm, 12mm, and 13mm), plastic storage rail
Socket Type (NP)	Low profile	Application	Fastening
Impact Rated	No	Package Type	Plastic storage rail
Measurement Type	Metric	Tool Features	Flex joint springs back to center and low profile
Material	Chrome-vanadium steel		
Finish	Chrome		
Insulated	No		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document