

T66860 Cut Sheet



TITAN AutoFlex low profile socket set, 12pt. internal hex, 7 pieces, chrome-vanadium steel, 1/4in drive, imperial, flex joint springs back to center and low profile, plastic storage rail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T66860>

Technical Specifications

Brand	TITAN
Series	AutoFlex
Item	Socket set
Number of Pieces	7
Socket Type (NP)	Low profile
Impact Rated	No
Measurement Type	Imperial
Material	Chrome-vanadium steel
Finish	Chrome
Insulated	No

Drive Size	1/4in
Tip Type	12pt. internal hex
Ratcheting	No
Set Includes	Includes (7) low profile 12pt socket set with autoflexing (3/16in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in, and 9/16in), plastic storage rail
Application	Fastening
Package Type	Plastic storage rail
Tool Features	Flex joint springs back to center and low profile

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document