

UR20-2AI-SG-24-DIAG Cut Sheet



Weidmuller UR20 series load cell input module, 2-channel, voltage, 24-bit resolution, input voltage signal range(s) of 0.5–30 mV/VDC. For use with 5 VDC 4- or 6-wire load cells. Removable terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR20-2AI-SG-24-DIAG>

Technical Specifications

Brand	Weidmuller
Item	Input module
I/O Module Type	Load cell
Series	UR20
Number Of Input Channels	2
Input Signal Type(s)	Voltage
Isolated Channels	Yes
Input Resolution	24-bit
Input Voltage Signal Range	0.5–30 mV/VDC
Sample Rate	5ms
For Use With	5 VDC 4- or 6-wire load cells
Includes	Removable terminal blocks
Programming Software	None, configure via Internet browser

Agency Approvals

UL Listed File #	E141197
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/UR20-2AI-SG-24-DIAG.pdf>
See store item page for other formats.