

UR20-2AI-UI-16 Cut Sheet



Weidmuller UR20 series analog input module, 2-channel, current/voltage, 16-bit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR20-2AI-UI-16>

Technical Specifications

Brand	Weidmuller
Item	Input module
I/O Module Type	Analog
Series	UR20
Number Of Input Channels	2
Input Signal Type(s)	Current/voltage
Isolated Channels	No
Number of Non-Isolated Input Commons	1

Input Resolution	16-bit
Input Current Signal Range	0–20 mA and 4–20 mA
Input Voltage Signal Range	0–5 VDC, 1–5 VDC, 0–10 VDC, 2–10 VDC, ±5 VDC and ±10 VDC
Includes	Removable terminal block
Programming Software	None, configure via Internet browser

Agency Approvals

UL Listed File #	E141197
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/UR20-2AI-UI-16.pdf>
See store item page for other formats.