

UR20-4COM-IO-LINK Cut Sheet



Weidmuller UR20 IO-Link master, (4) IO-Link capable I/O points, up to (4) discrete I/O points, IO-Link v1.1.2 (compatible with v1.1.3), 2A, 0.5A/port, plastic housing, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR20-4COM-IO-LINK>

Technical Specifications

Brand	Weidmuller
Item	IO-Link master
Series	UR20
Number of IO-Link Capable I/O Points	4
Number of Discrete I/O Points	Up to (4)
Discrete I/O Port Type(s)	(4) 4-pin terminal
Nominal Input Voltage	24 VDC
Discrete Input Type	Sinking
Number of Non-Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	4
Nominal Output Voltage	24 VDC
Discrete Output Type	Sourcing
Number of Non-Isolated Discrete Output Commons	1

Number of Points per Discrete Output Common	4
Communication Port and Connection Type(s)	(4) 4-pin terminal
Port Protocol(s)	IO-Link Class A Master
Port Speed(s)	• IO-Link COM1 • IO-Link COM2 • IO-Link COM3
IO-Link Version	IO-Link v1.1.2 (compatible with v1.1.3)
Amperage Rating	2A
Load Current	0.5A/port
Indicator	LED
Housing Material	Plastic
IP Rating	IP20
Programming Software	Weidmuller U-mation Configurator

Agency Approvals

UL Listed File #	E141197
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/UR20-4COM-IO-LINK.pdf>
See store item page for other formats.