

UR20-4RO-CO-255 Cut Sheet



Weidmuller UR20 series relay output module, 4-point, 277 VDC/277 VAC, (4) Form C, 4 common(s), 1 point(s) per common, 6A/point, 24A/module. Removable terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR20-4RO-CO-255>

Technical Specifications

Brand	Weidmuller
Item	Output module
I/O Module Type	Relay
Series	UR20
Number of Output Points	4
Nominal Output Voltage	277 VDC/277 VAC
Relay Configuration	(4) Form C (SPDT) relays
Number Of Commons	4

Jumper Selectable Isolation	No
Number of Points per Common	1
Load Current	6A/point, 24A/module
Fuse Type	User-supplied external fuse
Includes	Removable terminal blocks
Programming Software	None, configure via Internet browser

Agency Approvals

UL Listed File #	E141197
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/UR20-4RO-CO-255.pdf>
See store item page for other formats.