

UR20-8DIO-P-3W-DIAG Cut Sheet



Weidmuller UR20 series discrete combo module, Input: up to (8) points, 24 VDC, sinking/sourcing, Output: up to (8) points, 24 VDC, sourcing, 0.5A/point, 4A/common. Removable terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR20-8DIO-P-3W-DIAG>

Technical Specifications

Brand	Weidmuller
Item	Combo module
I/O Module Type	Discrete
Series	UR20
Number of Input Points	Up to (8)
Nominal Input Voltage	24 VDC
Discrete Input Type	Sinking/sourcing
Number of Non-Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	8

Number of Output Points	Up to (8)
Nominal Output Voltage	24 VDC
Discrete Output Type	Sourcing
Number of Non-Isolated Discrete Output Commons	1
Number of Points per Discrete Output Common	8
Load Current	0.5A/point, 4A/common
Includes	Removable terminal blocks
Programming Software	None, configure via Internet browser

Agency Approvals

UL Listed File #	E141197
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/UR20-8DIO-P-3W-DIAG.pdf>
See store item page for other formats.