



Weidmuller UR20 series bus coupler, 24 VDC, (2) Ethernet (RJ45) port(s), Modbus TCP, 100 Mbps. For use with Weidmuller UR20 series I/O modules.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR20-FBC-MOD-TCP-ECO>

Technical Specifications

Brand	Weidmuller	Number of Discrete Inputs/Outputs	256 inputs/256 outputs
Item	Bus coupler	Number of Analog Inputs/Outputs	128 inputs/64 outputs
Series	UR20	Maximum Number of Data Bytes	1000 process bytes/1000 parameter bytes/1000 diagnostic bytes
Voltage Rating	24 VDC	For Use With	Weidmuller UR20 series I/O modules
Number of Ports	2	Programming Software	None, configure via Internet browser
Communication Port and Connection Type(s)	(2) Ethernet (RJ45) port(s)		
Port Protocol(s)	Modbus TCP Slave		
Port Speed(s)	100 Mbps		

Agency Approvals

UL Listed File #	E141197
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/UR20-FBC-MOD-TCP-ECO.pdf>
See store item page for other formats.