

FLZ 510/520/530

Small Thermostats



17103000010

The FLZ series of thermostats are available with N.C., N.O., and change-over contacts. In combination with enclosure heaters, they serve for temperature control inside the enclosure. In combination with a Filterfans®, they provide additional savings on energy. DIN rail mounted for easy installation.

Features

- FLZ 510: Change-over contact with 3K switching differential (for fan and heater control)
- FLZ 520: N.C. contact (for heater control)
- FLZ 530: N.O. contact (for fan control)
- Bimetal probe type
- DIN rail mounted (35mm, EN 60715)
- UL recognized

Listings

- UL: E251765
- CSA: 1721048



FLZ 510/520/530 Small Thermostats						
Part Number	Price	Model	Type of Contact	Temp Range	Switching Diff	Drawing Link
<u>17103000010</u>	\$66.00	FLZ 510	change-over	32–140 °F (0–60 °C)	5.4 °F (3K)	PDF
<u>17111000010</u>	\$40.00	FLZ 520	N.C.	32–140 °F (0–60 °C)	12.6 °F (7K)	PDF
<u>17121000010</u>	\$40.00	FLZ 530	N.O.	32–140 °F (0–60 °C)	12.6 °F (7K)	PDF

FLZ 541-543 Twin Thermostats



17141000010

The FLZ 541-543 series integrates two independently switchable thermostats in one compact housing. Unlike thermostats with changeover contacts, connected devices can be switched in different temperature ranges. DIN rail mounted for easy installation.

Features

- FLZ 541: N.C./N.O. contacts (for fan and heater control)
- FLZ 542: N.C./N.C. contacts (for heaters/alarm)
- FLZ 543: N.O./N.O. contacts (for fans/alarm)
- Bimetal probe type; IP20
- DIN rail mounted (35mm, EN 60715)
- UL recognized

Listings

- UL: E251765
- CSA: 1721048



FLZ 541-543 Twin Thermostats							
Part Number	Price	Model	Contact 1	Contact 2	Temp Range	Switching Diff	Drawing Link
17141000010	\$66.00	FLZ 541	N.C.	N.O.	32–140 °F (0–60 °C)	12.6 °F (7K)	PDF
17142000010	\$66.00	FLZ 542	N.C.	N.C.	32–140 °F (0–60 °C)	12.6 °F (7K)	PDF
17143000010	\$66.00	FLZ 543	N.O.	N.O.	32–140 °F (0–60 °C)	12.6 °F (7K)	PDF

