

# Fan Heaters with Thermostat



## Features

- Designed to prevent condensation or maintain minimum temperature in enclosures.
- Built in Thermostat. (-18° C to +38° C) (0° F to +100° F).
- Fan Auto/On switch with pilot light for Heat On indication.
- High temperature safety protection.
- Aluminum alloy outer casing.
- Connection via terminal block.
- 1300W models are cURus approved only.

## Listings

- UL File E331157
- CSA File LR43697



Fan Heaters with Thermostat						
Part Number	Price	Watts	Voltage	Hz	CFM	Drawing Link
<a href="#">FLHTF125A115</a>	\$304.00	125W	120 VAC	60 Hz	20	<a href="#">PDF</a>
<a href="#">FLHTF200A115</a>	\$361.00	200W	120 VAC	60 Hz		<a href="#">PDF</a>
<a href="#">FLHTF400A115</a>	\$418.00	400W	120 VAC	60 Hz		<a href="#">PDF</a>
<a href="#">FLHTF800A115</a>	\$475.00	800W	120 VAC	60 Hz		<a href="#">PDF</a>
<a href="#">FLHTF1300A115</a>	\$502.00	1300W	120 VAC	60 Hz	50	<a href="#">PDF</a>
<a href="#">FLHTF125A230</a>	\$304.00	105/125W	220-240 VAC	50/60 Hz	20	<a href="#">PDF</a>
<a href="#">FLHTF200A230</a>	\$361.00	165/200W	220-240 VAC	50/60 Hz		<a href="#">PDF</a>
<a href="#">FLHTF400A230</a>	\$418.00	335/400W	220-240 VAC	50/60 Hz		<a href="#">PDF</a>
<a href="#">FLHTF800A230</a>	\$475.00	670/800W	220-240 VAC	50/60 Hz		<a href="#">PDF</a>
<a href="#">FLHTF1300A230</a>	\$502.00	1080/1300W	220-240 VAC	50/60 Hz	50	<a href="#">PDF</a>