

# NEMA 12 Double-Door Floor-Mount



## Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides some protection from falling dirt, dust, oil, and water.

## Construction

- Enclosures are formed steel - 14-gauge (54 in high), 12-gauge (60 in [1524 mm] high), or combination 10/12-gauge ( 72 in [1829 mm] high).
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Body stiffeners are provided in enclosures for extra rigidity.
- Heavy duty lifting eyebolts are provided with reinforced support angles.
- 12 in [305 mm] floor stands are welded to the enclosure.
- Welded brackets provide for enclosure mounting.
- Gasketed overlapping doors eliminate the need for a center post.
- Continuously hinged doors may be removed by pulling the hinge pin.
- Doors are secured with a 3-point latch and operated with a key locking/padlockable combo handle.
- Uses 1/4 turn latch handles.
- Latch rods are equipped with rollers for easier door closing.
- Oil-resistant gaskets are permanently secured.
- A removable 10-gauge subpanel is included in enclosures 60 in [1524 mm] and larger. Smaller sizes include a 12-gauge subpanel.
- Provision for light kit mounting.
- Panel supports are provided in enclosures 60 in [1524 mm] and larger for easy subpanel installation.
- Collar studs are provided for mounting subpanels.
- A grounding stud is provided in the enclosure for each door, and a bonding stud is provided on the door.
- A literature pocket is provided for the inside of the door.

## Finish

- Cover and enclosure are phosphatized and finished in recoatable smooth ANSI 61 gray powder coating.
- Removable subpanel is finished in RAL9003 white powder coating.

## Listings

- UL 508A Type 12 [UL File E65324]
- CSA Type 12 [CSA File LR21001]
- Complies with
  - NEMA Type 12
  - IEC 60529, IP54



# NEMA 12 Double-Door Floor-Mount




NEMA 12 Double-Door Floor-Mount				
Part Number	Price	Enclosure Size HxWxD	Subpanel Size HxW	Drawing Link
<a href="#">1422A8F</a>	\$1,922.00	54.13 x 42.06 x 9.90 [1375 x 1068 x 251]	50.00 x 38.00 [1270 x 965]	<a href="#">PDF</a>
<a href="#">1422B8F</a>	\$2,586.00	60.13 x 48.06 x 9.85 [1527 x 1221 x 250]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">1422B10F</a>	\$2,592.00	60.13 x 48.06 x 11.85 [1527 x 1221 x 301]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">1422B12F</a>	\$2,661.00	60.13 x 48.06 x 13.85 [1527 x 1221 x 352]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">1422B16F</a>	\$2,793.00	60.13 x 48.06 x 17.85 [1527 x 1221 x 453]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">1422B20F</a>	\$2,998.00	60.13 x 48.06 x 21.85 [1527 x 1221 x 555]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">1422B24F</a>	\$3,139.00	60.13 x 48.06 x 25.85 [1527 x 1221 x 657]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">1422D10F</a>	\$3,023.00	60.13 x 60.06 x 11.85 [1527 x 1526 x 301]	56.00 x 56.00 [1422 x 1422]	<a href="#">PDF</a>
<a href="#">1422D12F</a>	\$3,027.00	60.13 x 60.06 x 13.85 [1527 x 1526 x 352]	56.00 x 56.00 [1422 x 1422]	<a href="#">PDF</a>
<a href="#">1422D16F</a>	\$3,176.00	60.13 x 60.06 x 17.85 [1527 x 1526 x 453]	56.00 x 56.00 [1422 x 1422]	<a href="#">PDF</a>
<a href="#">1422D24F</a>	\$3,556.00	60.13 x 60.06 x 25.85 [1527 x 1526 x 657]	56.00 x 56.00 [1422 x 1422]	<a href="#">PDF</a>
<a href="#">1422E10F</a>	\$3,482.00	72.13 x 60.06 x 11.85 [1832 x 1526 x 301]	68.00 x 56.00 [1727 x 1422]	<a href="#">PDF</a>
<a href="#">1422E12F</a>	\$3,484.00	72.13 x 60.06 x 13.85 [1832 x 1526 x 352]	68.00 x 56.00 [1727 x 1422]	<a href="#">PDF</a>
<a href="#">1422E16F</a>	\$3,654.00	72.13 x 60.06 x 17.85 [1832 x 1526 x 453]	68.00 x 56.00 [1727 x 1422]	<a href="#">PDF</a>
<a href="#">1422E20F</a>	\$3,910.00	72.13 x 60.06 x 21.85 [1832 x 1526 x 555]	68.00 x 56.00 [1727 x 1422]	<a href="#">PDF</a>
<a href="#">1422E24F</a>	\$4,049.00	72.13 x 60.06 x 25.85 [1832 x 1526 x 657]	68.00 x 56.00 [1727 x 1422]	<a href="#">PDF</a>
<a href="#">1422F10F</a>	\$3,918.00	72.13 x 72.06 x 11.85 [1832 x 1830 x 301]	68.00 x 38.00 [1727 x 965]	<a href="#">PDF</a>
<a href="#">1422F12F</a>	\$3,922.00	72.13 x 72.06 x 13.85 [1832 x 1830 x 352]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>
<a href="#">1422F16F</a>	\$4,072.00	72.13 x 72.06 x 17.85 [1832 x 1830 x 453]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>
<a href="#">1422F20F</a>	\$4,307.00	72.13 x 72.06 x 21.85 [1832 x 1830 x 555]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>
<a href="#">1422F24F</a>	\$4,456.00	72.13 x 72.06 x 25.85 [1832 x 1830 x 657]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 12 Double-Door Floor-Mount



## Dimensions



# Enclosure Accessories

## Locks and Latches



### 1/4-Turn Latch Handles



#### Features

- Durable zinc diecast or stainless steel.
- Removable handle stop for clockwise / counter-clockwise operation.
- Textured powder coat Black finish on zinc cast handle.
- Maintains NEMA rating of enclosure.
- Padlock "trigger" design for security requirements.
- Optional key lock or defeater available. Key lock versions include two keys.

1/4-Turn Latch Handles							
Part Number	Price	Security Type	Latch Points	Material	Finish	For Use With These Hammond Enclosures Only	Drawing Link
<a href="#">MHK1</a>	\$127.00	padlocking	1	die-cast zinc	black matte	single-door NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD1</a>	\$133.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1</a>	\$144.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2</a>	\$217.00	padlocking	3	die-cast zinc	black matte	less than 60in (H) NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD2</a>	\$228.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2</a>	\$246.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3</a>	\$221.00	padlocking	3	die-cast zinc	black matte	60in (H) or greater NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD3</a>	\$232.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3</a>	\$251.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK1SS</a>	\$195.00	padlocking	1	316 stainless steel	#4 brush	single-door NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD1SS</a>	\$215.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1SS</a>	\$215.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2SS</a>	\$208.00	padlocking	3	316 stainless steel	#4 brush	less than 60in (H) NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD2SS</a>	\$229.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2SS</a>	\$229.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3SS</a>	\$302.00	padlocking	3	316 stainless steel	#4 brush	60in (H) or greater NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD3SS</a>	\$332.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3SS</a>	\$332.00	combination keylocking/ padlocking					<a href="#">PDF</a>