

# NEMA 1 Single-Door Wall-Mount with Knockouts 1/4-Turn Latch



## Applications

- Designed for general purpose indoor commercial use as a junction, pull or switch box.
- Hinged cover with latch provides easy access during installation and maintenance.

## Construction

- Formed and spot welded from 16- or 14-gauge steel depending on size.
- Formed steel covers close by use of slotted 1/4-turn latch.
- Full swing door using butt hinges.
- Easily removed knockouts on all four sides. See drawings for sizes and locations.
- Through holes in back for wall-mounting.
- Grounding location embossed in body.
- Uses N1JLK 1/4 turn latch.

## Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

## Listings

- UL-50 Type 1 [UL File 65324]
- CSA Type 1 [CSA File LR21001]
- Complies with
  - NEMA Type 1
  - IEC 60529, IP20




NEMA 1 Single-Door Wall-Mount with Knockouts 1/4-Turn Latch					
Part Number	Price	Enclosure Size HxWxD	Drawing Link	Side Pattern	Top Pattern
<a href="#">CHKO644</a>	\$13.50	6.38 x 4.30 x 4.12 [162 x 109 x 105]	<a href="#">PDF</a>	Z-X	Z-X-Z
<a href="#">CHKO663</a>	\$14.50	6.38 x 6.30 x 3.62 [162 x 160 x 92]	<a href="#">PDF</a>	Z-X-Z	Z-X-Z
<a href="#">CHKO664</a>	\$13.75	6.38 x 6.30 x 4.12 [162 x 160 x 105]	<a href="#">PDF</a>	Z-X-Z	Z-X-Z
<a href="#">CHKO666</a>	\$18.50	6.38 x 6.30 x 6.12 [162 x 160 x 155]	<a href="#">PDF</a>	Z-X-Z	Z-X-Z
<a href="#">CHKO864</a>	\$17.00	8.38 x 6.30 x 4.12 [213 x 160 x 105]	<a href="#">PDF</a>	Z-X-Z-X	Z-X-Z-X
<a href="#">CHKO884</a>	\$19.75	8.38 x 8.30 x 4.12 [213 x 211 x 105]	<a href="#">PDF</a>	Z-X-Z-X	Z-X-Z-X
<a href="#">CHKO886</a>	\$28.00	8.38 x 8.30 x 6.12 [213 x 211 x 155]	<a href="#">PDF</a>	Z-X-Z-X	Z-X-Z-X
<a href="#">CHKO1084</a>	\$24.50	10.38 x 8.30 x 4.12 [264 x 211 x 105]	<a href="#">PDF</a>	Z-X-Z-X	Z-X-Z-X
<a href="#">CHKO1086</a>	\$29.00	10.38 x 8.30 x 6.12 [264 x 211 x 155]	<a href="#">PDF</a>	Z-X-Z-X	Z-X-Z-X
<a href="#">CHKO10104</a>	\$27.00	10.38 x 10.30 x 4.12 [264 x 262 x 105]	<a href="#">PDF</a>	X-Z-Y-Z-X	Z-X-Z-X
<a href="#">CHKO10106</a>	\$33.00	10.38 x 10.30 x 6.12 [264 x 262 x 155]	<a href="#">PDF</a>	X-Z-Y-Z-X	Z-X-Z-X
<a href="#">CHKO1284</a>	\$28.00	12.38 x 8.30 x 4.12 [314 x 211 x 105]	<a href="#">PDF</a>	Z-X-Z-X	X-Z-Y-Z-X
<a href="#">CHKO12104</a>	\$34.00	12.38 x 10.30 x 4.12 [314 x 262 x 105]	<a href="#">PDF</a>	X-Z-Y-Z-X	X-Z-Y-Z-X
<a href="#">CHKO12106</a>	\$42.50	12.38 x 10.30 x 6.12 [314 x 262 x 155]	<a href="#">PDF</a>	X-Z-Y-Z-X	X-Z-Y-Z-X
<a href="#">CHKO12124</a>	\$32.50	12.38 x 12.30 x 4.11 [314 x 312 x 104]	<a href="#">PDF</a>	X-Z-Y-Z-X	X-Z-Y-Z-X
<a href="#">CHKO12126</a>	\$40.50	12.38 x 12.30 x 6.12 [314 x 312 x 155]	<a href="#">PDF</a>	X-Z-Y-Z-X	Z-X-Z-Y-Z-X-Z
<a href="#">CHKO16124</a>	\$40.50	16.38 x 12.30 x 4.11 [416 x 312 x 104]	<a href="#">PDF</a>	X-Z-Y-Z-X	Z-X-Z-Y-Z-X-Z
<a href="#">CHKO16126</a>	\$51.00	16.38 x 12.30 x 6.12 [416 x 312 x 155]	<a href="#">PDF</a>	X-Z-Y-Z-X	X-Z-Y-Z-X
<a href="#">CHKO16166</a>	\$57.00	16.38 x 16.30 x 6.12 [416 x 414 x 155]	<a href="#">PDF</a>	Z-X-Z-Y-Z-X-Z	Z-X-Z-Y-Z-X-Z
<a href="#">CHKO18124</a>	\$49.00	18.38 x 12.30 x 4.12 [467 x 312 x 105]	<a href="#">PDF</a>	X-Z-Y-Z-X	X-Z-X-Z-Y-Z-X-Z-X
<a href="#">CHKO18126</a>	\$57.00	18.38 x 12.30 x 6.12 [467 x 312 x 155]	<a href="#">PDF</a>	X-Z-Y-Z-X	X-Z-X-Z-Y-Z-X-Z-X
<a href="#">CHKO18186</a>	\$73.00	18.38 x 18.30 x 6.12 [467 x 465 x 155]	<a href="#">PDF</a>	X-Z-X-Z-Y-Z-X-Z-X	X-Z-X-Z-Y-Z-X-Z-X
<a href="#">CHKO24186</a>	\$133.00	24.38 x 18.30 x 6.12 [619 x 465 x 155]	<a href="#">PDF</a>	X-Z-X-Z-Y-Z-X-Z-X	X-Z-X-Z-Y-Z-X-Z-X
<a href="#">CHKO24246</a>	\$166.00	24.38 x 24.30 x 6.12 [619 x 617 x 155]	<a href="#">PDF</a>	X-Z-X-Z-Y-Z-X-Z-X	X-Z-X-Z-Y-Z-X-Z-X
<a href="#">CHKO30246</a>	\$199.00	30.38 x 24.30 x 6.12 [772 x 617 x 155]	<a href="#">PDF</a>	X-Z-X-Z-Y-Z-X-Z-X	X-Z-X-Z-Y-Z-X-Z-X
<a href="#">CHKO36246</a>	\$231.00	36.38 x 24.30 x 6.13 [924 x 617 x 156]	<a href="#">PDF</a>	X-Z-X-Z-Y-Z-X-Z-X	X-Z-X-Z-Y-Z-X-Z-X
<a href="#">CHKO36248</a>	\$249.00	36.38 x 24.30 x 8.13 [924 x 617 x 207]	<a href="#">PDF</a>	X-Z-X-Z-Y-Z-X-Z-X	X-Z-X-Z-Y-Z-X-Z-X

Note: Dimensions in inches [millimeters].


# NEMA 1 Single-Door Wall-Mount with Knockouts 1/4-Turn Latch



## Dimensions



### TYPICAL SIZES AND SPACING



SIZE & DISTANCE INFORMATION			
ID	INNER KNOCK-OUT	OUTER KNOCK-OUT	☉ DISTANCE
X	1.00 Ø	1.38 Ø	1.62 TYPICAL
Y	1.23 Ø	1.75 Ø	
Z	0.73 Ø	1.13 Ø	

# Enclosure Accessories Locks and Latches



## Padlock Kit



### Features

- Field installed kit requires drilling of only 4 holes.
- Compatible with 1414 and HJ enclosures.
- Only available in 316 stainless steel.
- Includes mounting hardware.
- Sold Individually.
- Installation instructions provided.

Padlock Kit		
Part Number	Price	Drawing Link
<a href="#">14PLKS16</a>	\$19.50	<a href="#">PDF</a>

## NEMA 1 Lock Kits



### Features

- Keylocking, 1-point, 1/4-turn, flush-mount latch.
- Installs in place of the existing slotted latch, or in cutout hole provided.
- Reversible cam position for other applications.
- Maintains NEMA 1 rating.

NEMA 1 Lock Kit				
Part Number	Price	Fits Enclosures	Material	Drawing Link
<a href="#">1427LKN1</a>	\$36.00	1420 and N1A	plated steel	<a href="#">PDF</a>
<a href="#">N1JLK</a>	\$9.50	N1J, CHKO, N1WS, N1WF, and SWB	polyamide	<a href="#">PDF</a>

## Padlock Adaptor

### EJ Series



### Features

- For use with Eclipse Junior (EJ) Series enclosures.
- Padlock adaptor fits directly over the slotted quarter turn preventing access.
- 2mm thick 14-gauge stainless steel.
- Stainless steel mounting hardware provided.
- Once installed, the bolts cannot be removed without the door open.
- Easy installed in the field.
- Padlock not included.
- Maintains UL/CSA Type 4, and 4X rating.

Padlock Adaptor Eclipse and Series 2000		
Part Number	Price	Drawing Link
<a href="#">EJPA</a>	\$20.50	<a href="#">PDF</a>

## Padlock Adaptor

### Eclipse and Series 2000



### Features

- For use with EN4SD /S2000 Series Enclosures.
- Padlock adaptor fits directly over the slotted quarter turn preventing access.
- 14-gauge 304 stainless steel.
- Stainless steel mounting hardware provided.
- Once installed, the bolts cannot be removed without the door open.
- Easy installed in the field.
- Padlock not included.
- Maintains UL/CSA Type 4 and 4X rating.

Padlock Adaptor EJ Series		
Part Number	Price	Drawing Link
<a href="#">EPA</a>	\$21.50	<a href="#">PDF</a>