

# NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Floor-Mount with 3-Point Handle



## Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

## Construction

- Formed 12-gauge 304 or 316 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Heavy duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges.
- 3-point padlocking door handle.
- Uses 1/4 turn latch handles.
- Seamless poured-in-place gasket.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the subpanel.
- 12 in [305 mm] floor stands are welded to the enclosure.

## Finish

- Cover and enclosure are natural stainless steel with a #4 smooth brushed finish.
- Removable 10-gauge subpanel is finished in RAL9003 white powder coating.

## Listings

- UL 508A Type 3R, 4X, and 12 [UL File E65324]
- CSA Type 3R, 4X, and 12 [CSA File LR21001]
- Complies with
  - NEMA Type 3R, 4X, 12 and 13
  - IEC 60529, IP66



## NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Floor-Mount with 3-Point Handle


304 Stainless	Price	316 Stainless	Price	Enclosure Size HxWxD	Subpanel HxW	Drawing Link
<a href="#">HN4FM604812SS</a>	\$6,030.00	<a href="#">HN4FM604812S16</a>	\$6,950.00	60.13 x 48.06 x 13.88 [1527 x 1221 x 353]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">HN4FM604818SS</a>	\$6,650.00	<a href="#">HN4FM604818S16</a>	\$7,665.00	60.13 x 48.06 x 19.88 [1527 x 1221 x 505]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">HN4FM606012SS</a>	\$6,806.00	<a href="#">HN4FM606012S16</a>	\$7,815.00	60.13 x 60.06 x 13.88 [1527 x 1526 x 353]	56.00 x 56.00 [1422 x 1422]	<a href="#">PDF</a>
<a href="#">HN4FM606018SS</a>	\$7,440.00	<a href="#">HN4FM606018S16</a>	\$8,396.00	60.13 x 60.06 x 19.88 [1527 x 1526 x 505]	56.00 x 56.00 [1422 x 1422]	<a href="#">PDF</a>
<a href="#">HN4FM726012SS</a>	\$8,166.00	<a href="#">HN4FM726012S16</a>	\$9,389.00	72.13 x 60.06 x 13.88 [1832 x 1526 x 353]	68.00 x 56.00 [1727 x 1422]	<a href="#">PDF</a>
<a href="#">HN4FM726018SS</a>	\$8,763.00	<a href="#">HN4FM726018S16</a>	\$9,463.00	72.13 x 60.06 x 19.88 [1832 x 1526 x 505]	68.00 x 56.00 [1727 x 1422]	<a href="#">PDF</a>
<a href="#">HN4FM727212SS</a>	\$8,441.00	<a href="#">HN4FM727212S16</a>	\$9,689.00	72.13 x 72.06 x 13.88 [1832 x 1830 x 353]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>
<a href="#">HN4FM727218SS</a>	\$9,184.00	<a href="#">HN4FM727218S16</a>	\$10,138.00	72.13 x 72.06 x 19.88 [1832 x 1830 x 505]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>
<a href="#">HN4FM727224SS</a>	\$10,638.00	<a href="#">HN4FM727224S16</a>	\$12,219.00	72.13 x 72.06 x 25.88 [1832 x 1830 x 657]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Floor-Mount with 3-Point Handle



## Dimensions



# Enclosure Accessories

## Locks and Latches



### 1/4-Turn Latch Handles



#### Features

- Durable zinc diecast or stainless steel.
- Removable handle stop for clockwise / counter-clockwise operation.
- Textured powder coat Black finish on zinc cast handle.
- Maintains NEMA rating of enclosure.
- Padlock "trigger" design for security requirements.
- Optional key lock or defeater available. Key lock versions include two keys.

1/4-Turn Latch Handles							
Part Number	Price	Security Type	Latch Points	Material	Finish	For Use With These Hammond Enclosures Only	Drawing Link
<a href="#">MHK1</a>	\$127.00	padlocking	1	die-cast zinc	black matte	single-door NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD1</a>	\$133.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1</a>	\$144.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2</a>	\$217.00	padlocking	3	die-cast zinc	black matte	less than 60in (H) NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD2</a>	\$228.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2</a>	\$246.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3</a>	\$221.00	padlocking	3	die-cast zinc	black matte	60in (H) or greater NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD3</a>	\$232.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3</a>	\$251.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK1SS</a>	\$195.00	padlocking	1	316 stainless steel	#4 brush	single-door NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD1SS</a>	\$215.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1SS</a>	\$215.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2SS</a>	\$208.00	padlocking	3	316 stainless steel	#4 brush	less than 60in (H) NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD2SS</a>	\$229.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2SS</a>	\$229.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3SS</a>	\$302.00	padlocking	3	316 stainless steel	#4 brush	60in (H) or greater NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD3SS</a>	\$332.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3SS</a>	\$332.00	combination keylocking/ padlocking					<a href="#">PDF</a>