


# NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



## Applications

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes, or terminal wiring enclosures.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

## Construction

- Formed 14-gauge 304 or 316 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Door stiffeners are provided in the larger enclosures for extra rigidity.
- Welded brackets provide for enclosure mounting.
- Formed lip on door and enclosure excludes flowing liquids and contaminants.
- Stainless steel continuous hinge on door may be removed by pulling the stainless steel hinge pin.
- Door is secured with easily operated stainless steel clamps.
- Provision for padlocking.
- Seamless poured-in-place gasket.
- A removable 12-gauge subpanel is included.
- Collar studs are provided for mounting subpanels.
- A bonding stud is provided on the door, and a grounding stud is provided in the enclosure.
- A literature pocket is provided for the inside of the door.

## Finish

- Cover and enclosure are natural stainless steel with a #4 smooth brushed finish.
- Removable subpanel is finished in RAL9003 white powder coating.

## Listings

- UL 508A Type 3R, 4, 4X, and 12 [UL File E65324]
- CSA Type 3R, 4, 4X, and 12 [CSA File LR21001]
- Complies with
  - NEMA Type 3R, 4, 4X, 12, and 13
  - IEC 60529, IP66



# NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount							
304 Stainless Steel	Price	316 Stainless Steel	Price	Enclosure Size HxWxD	Included Subpanel	Subpanel HxW	Drawing Link
<a href="#">1418N4SSB6</a>	\$631.00	<a href="#">1418N4S16B6</a>	\$691.00	16.00 x 12.00 x 7.20 [406 x 305 x 183]	<a href="#">18P1309</a>	13.00 x 9.00 [330 x 229]	<a href="#">PDF</a>
<a href="#">1418N4SSB8</a>	\$673.00	<a href="#">1418N4S16B8</a>	\$785.00	16.00 x 12.00 x 9.20 [406 x 305 x 234]	<a href="#">18P1309</a>	13.00 x 9.00 [330 x 229]	<a href="#">PDF</a>
<a href="#">1418N4SSG6</a>	\$701.00	<a href="#">1418N4S16G6</a>	\$816.00	16.00 x 16.00 x 7.20 [406 x 406 x 183]	<a href="#">18P1713</a>	17.00 x 13.00 [432 x 330]	<a href="#">PDF</a>
<a href="#">1418N4SSCR6</a>	\$774.00	<a href="#">1418N4S16CR6</a>	\$900.00	16.00 x 20.00 x 7.20 [406 x 508 x 183]	<a href="#">18P1713</a>	17.00 x 13.00 [432 x 330]	<a href="#">PDF</a>
<a href="#">1418N4SSC6</a>	\$774.00	<a href="#">1418N4S16C6</a>	\$846.00	20.00 x 16.00 x 7.20 [508 x 406 x 183]	<a href="#">18P1713</a>	17.00 x 13.00 [432 x 330]	<a href="#">PDF</a>
<a href="#">1418N4SSC8</a>	\$827.00	<a href="#">1418N4S16C8</a>	\$904.00	20.00 x 16.00 x 9.20 [508 x 406 x 234]	<a href="#">18P1713</a>	17.00 x 13.00 [432 x 330]	<a href="#">PDF</a>
<a href="#">1418N4SSC10</a>	\$880.00	<a href="#">1418N4S16C10</a>	\$1,024.00	20.00 x 16.00 x 11.20 [508 x 406 x 284]	<a href="#">18P1713</a>	17.00 x 13.00 [432 x 330]	<a href="#">PDF</a>
<a href="#">1418N4SSD6</a>	\$857.00	<a href="#">1418N4S16D6</a>	\$995.00	20.00 x 20.00 x 7.20 [508 x 508 x 183]	<a href="#">18P1717</a>	17.00 x 17.00 [432 x 432]	<a href="#">PDF</a>
<a href="#">1418N4SSD8</a>	\$943.00	<a href="#">1418N4S16D8</a>	\$1,057.00	20.00 x 20.00 x 9.20 [508 x 508 x 234]	<a href="#">18P1717</a>	17.00 x 17.00 [432 x 432]	<a href="#">PDF</a>
<a href="#">1418N4SSER8</a>	\$1,177.00	<a href="#">1418N4S16ER8</a>	\$1,358.00	20.00 x 24.00 x 9.20 [508 x 610 x 234]	<a href="#">18P1717</a>	17.00 x 17.00 [432 x 432]	<a href="#">PDF</a>
<a href="#">1418N4SSH8</a>	\$1,081.00	<a href="#">1418N4S16H8</a>	\$1,247.00	24.00 x 16.00 x 9.20 [610 x 406 x 234]	<a href="#">18P2113</a>	21.00 x 13.00 [533 x 330]	<a href="#">PDF</a>
<a href="#">1418N4SSE10</a>	\$1,078.00	<a href="#">1418N4S16E10</a>	\$1,430.00	24.00 x 20.00 x 11.20 [610 x 508 x 284]	<a href="#">18P2117</a>	21.00 x 17.00 [533 x 432]	<a href="#">PDF</a>
<a href="#">1418N4SSE6</a>	\$1,116.00	<a href="#">1418N4S16E6</a>	\$1,289.00	24.00 x 20.00 x 7.20 [610 x 508 x 183]	<a href="#">18P2117</a>	21.00 x 17.00 [533 x 432]	<a href="#">PDF</a>
<a href="#">1418N4SSE8</a>	\$1,177.00	<a href="#">1418N4S16E8</a>	\$1,106.00	24.00 x 20.00 x 9.20 [610 x 508 x 234]	<a href="#">18P2117</a>	21.00 x 17.00 [533 x 432]	<a href="#">PDF</a>
<a href="#">1418N4SSJ6</a>	\$1,239.00	<a href="#">1418N4S16J6</a>	\$1,393.00	24.00 x 24.00 x 7.20 [610 x 610 x 183]	<a href="#">18P2121</a>	21.00 x 21.00 [533 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSJ8</a>	\$1,268.00	<a href="#">1418N4S16J8</a>	\$1,401.00	24.00 x 24.00 x 9.20 [610 x 610 x 234]	<a href="#">18P2121</a>	21.00 x 21.00 [533 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSJ12</a>	\$1,396.00	<a href="#">1418N4S16J12</a>	\$1,624.00	24.00 x 24.00 x 13.20 [610 x 610 x 335]	<a href="#">18P2121</a>	21.00 x 21.00 [533 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSKR8</a>	\$1,407.00	<a href="#">1418N4S16KR8</a>	\$1,635.00	24.00 x 30.00 x 9.20 [610 x 762 x 234]	<a href="#">18P2721</a>	27.00 x 21.00 [686 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSF8</a>	\$1,298.00	<a href="#">1418N4S16F8</a>	\$1,504.00	30.00 x 20.00 x 9.20 [762 x 508 x 234]	<a href="#">18P2717</a>	27.00 x 17.00 [686 x 432]	<a href="#">PDF</a>
<a href="#">1418N4SSK8</a>	\$1,407.00	<a href="#">1418N4S16K8</a>	\$1,557.00	30.00 x 24.00 x 9.20 [762 x 610 x 234]	<a href="#">18P2721</a>	27.00 x 21.00 [686 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSK10</a>	\$1,513.00	<a href="#">1418N4S16K10</a>	\$1,713.00	30.00 x 24.00 x 11.20 [762 x 610 x 284]	<a href="#">18P2721</a>	27.00 x 21.00 [686 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSK12</a>	\$1,548.00	<a href="#">1418N4S16K12</a>	\$1,717.00	30.00 x 24.00 x 13.20 [762 x 610 x 335]	<a href="#">18P2721</a>	27.00 x 21.00 [686 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSK16</a>	\$1,691.00	<a href="#">1418N4S16K16</a>	\$1,981.00	30.00 x 24.00 x 17.20 [762 x 610 x 437]	<a href="#">18P2721</a>	27.00 x 21.00 [686 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSKK8</a>	\$1,580.00	<a href="#">1418N4S16KK8</a>	\$1,841.00	30.00 x 30.00 x 9.20 [762 x 762 x 234]	<a href="#">18P2727</a>	27.00 x 27.00 [686 x 686]	<a href="#">PDF</a>
<a href="#">1418N4SSL8</a>	\$1,544.00	<a href="#">1418N4S16L8</a>	\$1,798.00	36.00 x 24.00 x 9.20 [914 x 610 x 234]	<a href="#">18P3321</a>	33.00 x 21.00 [838 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSL10</a>	\$1,624.00	<a href="#">1418N4S16L10</a>	\$1,896.00	36.00 x 24.00 x 11.20 [914 x 610 x 284]	<a href="#">18P3321</a>	33.00 x 21.00 [838 x 533]	<a href="#">PDF</a>
<a href="#">1418N4SSM8</a>	\$1,743.00	<a href="#">1418N4S16M8</a>	\$1,935.00	36.00 x 30.00 x 9.20 [914 x 762 x 234]	<a href="#">18P3327</a>	33.00 x 27.00 [838 x 686]	<a href="#">PDF</a>
<a href="#">1418N4SSM10</a>	\$1,828.00	<a href="#">1418N4S16M10</a>	\$2,140.00	36.00 x 30.00 x 11.20 [914 x 762 x 284]	<a href="#">18P3327</a>	33.00 x 27.00 [838 x 686]	<a href="#">PDF</a>
<a href="#">1418N4SSLL12</a>	\$2,123.00	<a href="#">1418N4S16LL12</a>	\$2,493.00	36.00 x 36.00 x 13.20 [914 x 914 x 335]	<a href="#">18P3327</a>	33.00 x 27.00 [838 x 686]	<a href="#">PDF</a>
<a href="#">1418N4SSM12</a>	\$1,917.00	<a href="#">1418N4S16M12</a>	\$2,246.00	36.00 x 30.00 x 13.20 [914 x 762 x 335]	<a href="#">18P3327</a>	33.00 x 27.00 [838 x 686]	<a href="#">PDF</a>
<a href="#">1418N4SSM16</a>	\$2,090.00	<a href="#">1418N4S16M16</a>	\$2,458.00	36.00 x 30.00 x 17.20 [914 x 762 x 437]	<a href="#">18P3327</a>	33.00 x 27.00 [838 x 686]	<a href="#">PDF</a>
<a href="#">1418N4SSO10</a>	\$2,001.00	<a href="#">1418N4S16O10</a>	\$2,345.00	42.00 x 30.00 x 11.20 [1067 x 762 x 284]	<a href="#">18P3927</a>	39.00 x 27.00 [991 x 686]	<a href="#">PDF</a>
<a href="#">1418N4SSP8</a>	\$2,121.00	<a href="#">1418N4S16P8</a>	\$2,471.00	42.00 x 36.00 x 9.20 [1067 x 914 x 234]	<a href="#">18P3933</a>	39.00 x 33.00 [991 x 838]	<a href="#">PDF</a>
<a href="#">1418N4SSS8</a>	\$2,311.00	<a href="#">1418N4S16S8</a>	\$2,715.00	48.00 x 36.00 x 9.20 [1219 x 914 x 234]	<a href="#">18P4533</a>	45.00 x 33.00 [1143 x 838]	<a href="#">PDF</a>
<a href="#">1418N4SSS10</a>	\$2,529.00	<a href="#">1418N4S16S10</a>	\$2,883.00	48.00 x 36.00 x 11.20 [1219 x 914 x 284]	<a href="#">18P4533</a>	45.00 x 33.00 [1143 x 838]	<a href="#">PDF</a>
<a href="#">1418N4SSS12</a>	\$2,538.00	<a href="#">1418N4S16S12</a>	\$2,984.00	48.00 x 36.00 x 13.20 [1219 x 914 x 335]	<a href="#">18P4533</a>	45.00 x 33.00 [1143 x 838]	<a href="#">PDF</a>
<a href="#">1418N4SSS16</a>	\$2,786.00	<a href="#">1418N4S16S16</a>	\$3,084.00	48.00 x 36.00 x 17.20 [1219 x 914 x 437]	<a href="#">18P4533</a>	45.00 x 33.00 [1143 x 838]	<a href="#">PDF</a>
<a href="#">1418N4SST12</a>	\$3,002.00	<a href="#">1418N4S16T12</a>	\$3,533.00	60.00 x 36.00 x 13.20 [1524 x 914 x 335]	<a href="#">18P5733</a>	57.00 x 33.00 [1448 x 838]	<a href="#">PDF</a>
<a href="#">1418N4SST16</a>	\$3,433.00	<a href="#">1418N4S16T16</a>	\$3,872.00	60.00 x 36.00 x 17.20 [1524 x 914 x 437]	<a href="#">18P5733</a>	57.00 x 33.00 [1448 x 838]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Wall-Mount



## Dimensions

