

MAUN Pliers & Cutting Tools

Diagonal Cutters

Maun's PVC Comfort Grip diagonal cutters deliver high-leverage cutting for soft and hard wire — built for engineers, electricians, and technicians who cut wire daily in panel and machine builds. Compound-lever action multiplies hand force (18x on the 140mm, 22x on the 160mm) to cut with far less effort than a conventional plier of the same size. Induction-hardened jaws hold an accurate edge through heavy daily use, while zinc-plated handles with soft PVC grips keep the tool comfortable to operate regardless of hand size.

Features

- Compound-lever action multiplies hand force up to 22x for effortless cutting of hard wire
- Induction-hardened jaws to HRC 64 for accurate, long-lasting cutting edges
- Long-lasting return spring for consistent jaw positioning
- Zinc-plated handles with PVC comfort grips
- Rust-resistant finish for reliable long-term performance
- Meets BS 3087-7:1996 and ISO 5747:1995
- Available in 140mm and 160mm lengths to match wire type and cutting capacity



Pliers & Cutting Tools									
Part Number	Part Image	Pliers Type	Overall Length	Jaw Length	Jaw Opening	Jaw Width	Jaw Thickness	Cutting Capacity	Price
<u>2999-140</u>		Diagonal	5.5in [140mm]	0.64in [16.3mm]	0.31in [8.0mm]	0.95in [24.2mm]	0.31in [8.0mm]	2.0mm piano wire 4.0mm soft wire	\$73.00
<u>2999-160</u>		Diagonal	6.3in [160mm]	0.64in [16.3mm]	0.31in [8.0mm]	0.95in [24.2mm]	0.31in [8.0mm]	2.0mm piano wire 4.0mm soft wire	\$80.00