

MAUN Pliers & Cutting Tools

Parallel-Action Pliers with Cutters

Maun's side cutter parallel pliers combine cutting and gripping in a single tool — the classic combination plier, reimagined. Parallel-action, serrated jaws grip evenly along their full length, while a compound-lever cutting jaw multiplies hand force up to 23x for easier cuts on hard wire. An open throat lets cable, rod, and studding pass through the tool, and induction-hardened cutting edges hold an accurate, lasting edge.

Features

- Compound-lever cutting jaw multiplies hand force up to 23x for easier cuts on hard wire
- Induction-hardened cutting edges for accurate, long-lasting cuts
- Parallel-action, serrated jaws grip evenly along the full jaw length on square and hex fastenings
- Open throat passes cable, rod, and studding through the tool
- Red comfort-grip handles reduce hand fatigue



Pliers & Cutting Tools									
Part Number	Part Image	Pliers Type	Overall Length	Jaw Length	Jaw Opening	Jaw Width	Jaw Thickness	Cutting Capacity	Price
4961-125		Parallel Flat Nose	4.9in [125mm]	1.18in [30.0mm]	0.39in [10.0mm]	1.34in [34.0mm]	0.25in [6.4mm]	1.6mm piano wire 3.0mm soft wire	\$75.00
4961-160		Parallel Flat Nose	6.3in [160mm]	1.33in [34.0mm]	0.55in [14.0mm]	1.53in [39.0mm]	0.35in [9.0mm]	2.0mm piano wire 4.0mm soft wire	\$82.00
4961-200		Parallel Flat Nose	7.9in [200mm]	1.57in [40.0mm]	0.67in [17.0mm]	1.94in [49.3mm]	0.49in [12.5mm]	2.5mm piano wire 6.0mm soft wire	\$106.00