

Subpanels for Heartland Series Enclosures

Aluminum Subpanels

- Material: 3003-H14 aluminum
- Finish: Mill



Aluminum Subpanels				
Part Number	Price	Subpanel Size HxW	Fits Enclosures	Drawing Link
BP66A		4.88 x 4.88 [124 x 124]	AH6*, AHF6*, CL7*, DS6*, DSCC60604HPL, F4PBW, J606*, JW606HPL and RJ606*	PDF
BP86A		6.88 x 4.88 [175 x 124]	AH86*, AHF86*, CL9*, DS806*, F6PBW, J806*, JW806*, RJ806* and RJW806HPL	PDF
BP88A		6.88 x 6.88 [175 x 175]	AH88*, AHF88*, DS808*, DSCC80804HPL, J808SSH, J808*, J808W and RJ808HPL	PDF
BP108A		8.88 x 6.88 [226 x 175]	AH108*, AHF108*, CL11*, DS10*, DSCC1008HLL, DSW10*, F9PBW, J10*, JW10*, RJ10*, RJW1008HPL and WH-J1008HPL	PDF
BP1010A		8.88 x 8.88 [226 x 226]	AH1010*, AHF1010* and AHWD10106	PDF
BP1210A		10.88 x 8.88 [276 x 226]	AH12*, AHF12*, AHWD12106, CL13*, DS12*, DSCC121006HPL, DSW121006HPL, J1210*, JW12*, RJ12*, RJW1210HPL and WH-J1210HPL	PDF
BP1412A		12.88 x 10.88 [327 x 276]	AH14*, AHF14*, AHWD14126, CL15*, DS1412*, DSCC141206HPL, DSW14*, J14*, JW14*, RJ14*, RJW14* and WH-J1412HPL	PDF
BP1614A		14.88 x 12.88 [378 x 327]	AH16*, AHF16*, AHWD16148, DS1614*, DSCC161408HPL, DSW1614*, J16*, JW16*, RJ16*, RJW16* and WH-J1614HPL	PDF
BP1816A		16.88 x 14.88 [429 x 378]	AH18*, AHF18*, AHWD181610, DS18*, DSW18*, J18*, JW1816*, RJ18*, RJW18* and WH-J1816HPL	PDF
BP2016A		18.88 x 14.88 [480 x 378]	AH20*, AHF20*, AHWD20168, DS20*, J20*, JW2016HLL, RJ20* and RJW2016HPL	PDF
BP2424A		22.88 x 22.88 [581 x 581]	AH24* and AHWD242410	PDF

Note: Dimensions in inches (millimeters).

**BP66A**

Aluminum Swing Panel Kits

- Material: 3003-H14 aluminum
- Finish: Mill
- Includes swing panel, (4) AHSPM brackets and mounting screws

Aluminum Swing Panel Kits				
Part Number	Price	Subpanel Size HxW	Fits Enclosures	Drawing Link
AH66SPK		5.63 x 5.63 [143 x 143]	AH66* and AHF66*	PDF
AH86SPK		7.63 x 5.63 [194 x 143]	AH86* and AHF86*	PDF
AH88SPK		7.63 x 7.63 [194 x 194]	AH884xxx Heartland series	PDF
AH108SPK		9.63 x 7.63 [245 x 194]	AH108* and AHF108*	PDF
AH1010SPK		9.63 x 9.63 [245 x 245]	AH1010*, AHF1010* and AHWD10106	PDF
AH1210SPK		11.63 x 9.63 [295 x 245]	AH12*, AHF12* and AHWD12106	PDF
AH1412SPK		13.63 x 11.63 [346 x 295]	AH14*, AHF14* and AHWD14126	PDF
AH1614SPK		15.63 x 13.63 [397 x 346]	AH16*, AHF16* and AHWD16148	PDF
AH1816SPK		17.63 x 15.63 [448 x 397]	AH18*, AHF18* and AHWD181610	PDF
AH2016SPK		19.63 x 15.63 [499 x 397]	AH20*, AHF20* and AHWD20168	PDF
AH2424SPK		23.63 x 23.63 [600 x 600]	AH24* and AHWD242410	PDF

Note: Dimensions in inches (millimeters).
Not compatible with Heartland SL enclosures

**AH66SPK**

Subpanels for Heartland Series Enclosures

Aluminum Side Panels

- Material: 3003-H14 aluminum
- Finish: Mill



Aluminum Subpanels				
Part Number	Price	Subpanel Size HxW	Fits Enclosures	Drawing Link
SP6		5.00 x 3.00 [127 x 76]	AH6* and AHF6*	PDF
SP8		7.00 x 3.00 [178 x 76]	AH8* and AHF8*	PDF
SP10		9.00 x 3.50 [229 x 89]	AH1084*, AH1086*, AH1010*, AHF1084*, AHF1086* and AHF1010*	PDF
SP12		11.00 x 5.00 [279 x 127]	AH12106* and AHF12106*	PDF
SP14		13.00 x 5.00 [330 x 127]	AH14126* and AHF14126*	PDF
SP16		15.00 x 7.00 [381 x 178]	AH16148* and AHF16148*	PDF
SP18		17.00 x 9.00 [432 x 229]	AH181610* and AHF181610*	PDF
SP20		19.00 x 7.00 [483 x 178]	AH20168* and AHF20168*	PDF
SP24		23.00 x 9.00 [584 x 229]	AH24*	PDF
Note: Dimensions in inches (millimeters). Corrosion resistant slot nut fastening hardware kit included				

[SP8](#)

ABS Plastic Subpanels

- Material: ABS plastic
- Finish: Mill

ABS plastic Subpanels				
Part Number	Price	Subpanel Size HxW	Fits Enclosures	Drawing Link
BP66ABS		4.75 x 4.75 [121 x 121]	AH6*, AHF6*, CL7*, DS6*, DSCC60604HPL, F4PBW, J606*, JW606HPL and RJ606*	PDF
BP86ABS		6.75 x 4.75 [171 x 121]	AH86*, AHF86*, CL9*, DS806*, F6PBW, J806*, JW806*, RJ806* and RJW806HPL	PDF
BP108ABS		8.75 x 6.75 [222 x 171]	AH108*, AHF108*, CL11*, DS10*, DSCC1008HLL, DSW10*, F9PBW, J10*, JW10*, RJ10*, RJW1008HPL and WH-J1008HPL	PDF
BP1010ABS		8.75 x 8.75 [222 x 222]	AH1010*, AHF1010* and AHWD10106	PDF
BP1210ABS		10.75 x 8.75 [273 x 222]	AH12*, AHF12*, AHWD12106, CL13*, DS12*, DSCC121006HPL, DSW121006HPL, J1210*, JW12*, RJ12*, RJW1210HPL and WH-J1210HPL	PDF
BP1412ABS		12.75 x 10.75 [324 x 273]	AH14*, AHF14*, AHWD14126, CL15*, DS1412*, DSCC141206HPL, DSW14*, J14*, JW14*, RJ14*, RJW14* and WH-J1412HPL	PDF
BP1614ABS		14.75 x 12.75 [375 x 324]	AH16*, AHF16*, AHWD16148, DS1614*, DSCC161408HPL, DSW1614*, J16*, JW16*, RJ16*, RJW16* and WH-J1614HPL	PDF
BP1816ABS		16.75 x 14.75 [425 x 375]	AH18*, AHF18*, AHWD181610, DS18*, DSW18*, J18*, JW1816*, RJ18*, RJW18* and WH-J1816HPL	PDF
BP2016ABS		18.75 x 14.75 [476 x 375]	AH20*, AHF20*, AHWD20168, DS20*, J20*, JW2016HLL, RJ20* and RJW2016HPL	PDF
BP2424ABS		22.75 x 22.75 [578 x 578]	AH24* and AHWD242410	PDF
Note: Dimensions in inches (millimeters).				

[BP108ABS](#)