



Zyklop Speed Ratchet



Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



Swivel ratchet head


The ratchet head pivots freely and locks at 0°, 15° and 90°, making it possible to work in confined spaces with ample hand clearance.



Simple direction change

Rotating the large thumbwheel quickly changes rotation from clockwise to counterclockwise from any position of the ratchet head.

| Wera Speed Ratchets | | |
|------------------------------------|---|-------|
| Part Number | Description | Price |
| <u>05003500055</u> | Wera Zyklop Speed ratchet, 1/4 inch drive, with locking swivel head and ergonomic grip handle. Manufacturer part number 003500. | |
| <u>05003550055</u> | Wera Zyklop Speed ratchet, 3/8 inch drive, with locking swivel head and ergonomic grip handle. Manufacturer part number 003550. | |
| <u>05003600055</u> | Wera Zyklop Speed ratchet, 1/2 inch drive, with locking swivel head and ergonomic grip handle. Manufacturer part number 003600. | |



Unbelievably fast


The gyrating mass design along with the Kraftform handle and free-turning sleeve allow for rapid rotation when used as a screwdriver.



Zyklop Speed Ratchet and Socket Sets



3/8 inch Drive Ratchet Sets



| 3/8 inch Drive Ratchet Sets | | |
|-----------------------------|---|------------|
| Part Number | Description | Price Each |
| 05003596055 | Wera driver bit and socket set with Zyklop Speed ratchet, 3/8 inch drive, SAE. 38 pieces. Sturdy metal case included. Manufacturer part number 003596. | |
| 05003594055 | Wera driver bit and socket set with Zyklop Speed ratchet, 3/8 inch drive, metric. 43 pieces. Sturdy metal case included. Manufacturer part number 003594. | |

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect.



Wera driver bit and socket set with Zyklop Speed ratchet, 3/8 inch drive, metric, 43 pieces. Includes the pieces listed in the table below.

| 05003596055 Contents | | |
|----------------------|--------------------------|---|
| | 3/8 Zyklop Speed ratchet | |
| | Sliding T-handle | 3/8 x 165 |
| | 6-point socket | 1/4 x 29, 5/16 x 29, 11/32 x 29, 3/8 x 29, 7/16 x 29, 1/2 x 29, 9/16 x 29, 5/8 x 30, 11/16 x 30, 3/4 x 30, 13/16 x 30, 7/8 x 30 |
| | Wobble extension | 3/8 x 76 |
| | Universal joint | 3/8 x 50 |
| | Lockable extension | 3/8 x 200, 3/8 x 125 |
| | Bit adaptor | 1/4 x 3/8 x 44 |
| | Slotted bit | 1.0 x 5.5 x 25 |
| | Hex-Plus bit, 25mm long | 5/64, 3/32, 1/8, 9/64, 5/32, 3/16, 7/32 |
| | Phillips bit, 25mm long | PH2, PH3 |
| | Posidriv bit, 25mm long | PZ2, PZ3 |
| | Torx® bit, 25mm long | TX10, TX15, TX20, TX25, TX27, TX30, TX40 |

Wera driver bit and socket set with Zyklop Speed ratchet, 3/8 inch drive, SAE, 38 pieces. Includes the pieces listed in the table below.

| 05003594055 Contents | | |
|----------------------|--------------------------|--|
| | 3/8 Zyklop Speed ratchet | |
| | Sliding T-handle | 3/8 x 165 |
| | 6-point socket | 6 x 29, 7 x 29, 8 x 29, 9 x 29, 10 x 29, 11 x 29, 12 x 29, 13 x 29, 14 x 29, 15 x 29, 16 x 30, 17 x 30, 18 x 30, 19 x 30, 20 x 30, 21 x 30, 22 x 30, 24 x 30 |
| | Wobble extension | 3/8 x 76 |
| | Universal joint | 3/8 x 50 |
| | Lockable extension | 3/8 x 200, 3/8 x 125 |
| | Bit adaptor | 1/4 x 3/8 x 44 |
| | Slotted bit | 1.0 x 5.5 x 25 |
| | Hex-Plus bit, 25mm long | 3, 4, 5, 6, 8, 10 |
| | Phillips bit, 25mm long | PH2, PH3 |
| | Posidriv® bit, 25mm long | PZ2, PZ3 |
| | Torx® bit, 25mm long | TX10, TX15, TX20, TX25, TX27, TX30, TX40 |

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.